



To use the MTC for remote switching using Outputs 1,2, and/or 3 a relay is needed. The Siren Marine DC Relay (PAM-4) meets this need for most DC accessories. *Outputs 1,2, and 3 are rated for 1 amp.*

Wiring Instructions:

- 1.) The Red and Black wires are the coil side of the relay.
 - a.) Red connects to +V (Positive Voltage)
 - b.) Black connects to Output 1,2, or 3

- 2.) The Blue and Orange wires are the switch side of the relay
 - a.) Blue connects to +V
 - b.) Orange connects to the accessory

Siren Marine MTC

Wiring for external relay to control electrical devices with output 1,2,3.

Revision 4
February 2018